

Rotary Tablet Compression Machine

Features

- Particles fall within the 20 to 60 mesh range.
- Adhesion If the raw material doesn't have adhesion, please increase it.
- The raw materials must be in dry powder form and the moisture content must be controlled below 5%.



Technical Specification

Filling Accuracy	1 (%)
Power	6Kw
Packing Volume	5 (L)
Subpackaging Capacity	1 (ml)
Applicable Industries	Daily chemicals, medicine
Filling Apeed	10000 to 150000
Packing Type	Capsules, tablet
Weight	960kg
Host Size(L x W x H)	480mm*630mm*1100mm

